



- ▶ Unique spiral design shortens the length of the lamp
- ▶ Minimal light trapping creating more light output
- ▶ Light distribution very close to incandescent
- ▶ Operating temperatures: -18°C/0°F to 50°C/123°F



Order code	Description	Watts ¹ (W)	Base	Colour temp. (K)	CRI	Average life (hrs)	Initial lumens (lm)	Case qty	Incandescent equivalent (W)
------------	-------------	---------------------------	------	---------------------	-----	-----------------------	------------------------	----------	--------------------------------

High Wattage Spirals

32 W: MOL : 6 3/32 in. (155 mm) Dia. : 2 3/8 in. (67 mm)

60932	CF32/27K/SPIRAL/E26/STD	32	E26	2 700	82	10 000	2 000	48	120
56274	CF32/30K/SPIRAL/E26/STD	32	E26	3 000	82	10 000	2 100	48	120
58410	CF32/35K/SPIRAL/E26/STD	32	E26	3 500	82	10 000	2 100	48	120
58411	CF32/41K/SPIRAL/E26/STD	32	E26	4 100	82	10 000	2 100	48	120
60936	CF32/50K/SPIRAL/E26/STD	32	E26	5 000	82	10 000	2 000	48	120
58412	CF32/65K/SPIRAL/E26/STD	32	E26	6 500	82	10 000	2 100	48	120

40 W: MOL : 7 3/32 in. (185 mm) Dia. : 2 3/8 in. (67 mm)

60939	CF40/30K/SPIRAL/E26/STD	40	E26	3 000	82	10 000	2 600	48	150
60940	CF40/35K/SPIRAL/E26/STD	40	E26	3 500	82	10 000	2 600	48	150
60941	CF40/41K/SPIRAL/E26/STD	40	E26	4 100	82	10 000	2 600	48	150
60942	CF40/50K/SPIRAL/E26/STD	40	E26	5 000	82	10 000	2 600	48	150
60943	CF40/65K/SPIRAL/E26/STD	40	E26	6 500	82	10 000	2 600	48	150

55 W: MOL : 9 29/32 in. (245 mm) Dia. : 3 3/32 in. (80 mm)

60922	CFL55/27K/SPIRAL/E26/STD	55	E26	2 700	82	10 000	3 700	48	300
60923	CFL55/50K/SPIRAL/E26/STD	55	E26	5 000	82	10 000	3 700	48	300

65 W: MOL : 9 7/16 in. (240 mm) Dia. : 3 7/32 in. (90 mm)

60924	CFL65/27K/SPIRAL/E26/STD	65	E26	2 700	82	10 000	4 300	48	300
60925	CFL65/50K/SPIRAL/E26/STD	65	E26	5 000	82	10 000	4 300	48	300

85 W: MOL : 9 31/32 in. (253 mm) Dia. : 4 1/2 in. (102 mm)

60926	CFL85/27K/SPIRAL/E26/STD	85	E26	2 700	82	10 000	5 400	12	350
60927	CFL85/50K/SPIRAL/E26/STD	85	E26	5 000	82	10 000	5 400	12	350

105 W: MOL : 11 1/4 in. (286 mm) Dia. : 4 1/2 in. (102 mm)

60928	CFL105/27K/SPIRAL/E39/STD	105	E39	2 700	82	10 000	6 500	12	400
60929	CFL105/50K/SPIRAL/E39/STD	105	E39	5 000	82	10 000	6 500	12	400



High Wattage Spiral Lamps