

ORDERING INFORMATION


Order code: 63798
 Description: H35/PAR30/ECO/FL/120V/STD
 UPC: 69549637986
 Case quantity: 15

- ▶ Estimated Energy Cost per year: \$4.22
- ▶ Life in years*: 1.8 years
- ▶ Replaces a 50 Watts Halogen PAR lamp
- ▶ Provides a crisp white light



LAMP CHARACTERISTICS

Type:	Energy Saving PAR (ECO)
Shape:	PAR30
Base:	E26
Lens finish:	Clear
Reflector finish:	Silver
Filament Shape:	CC-8
Lamp material:	Hard glass
Beam angle:	35°



MOL : 3 17/32 in. (90 mm) Dia. : 3 1/4 in. (95 mm)

PERFORMANCE DATA

Watts:	35 W
Voltage:	120 V
Colour temperature (K):	2 900
Colour Rendering Index (CRI):	100
Average life (hours):	2 000
Operating position:	Universal
Initial lumen (lm):	500
Center Beam Candle Power (CBCP):	300



*Based on 3 hours per day usage

CAUTION

For indoor or outdoor use, where not directly exposed to weather. Do not use lamp if outer glass is scratched or broken to avoid breakage. Even though lamp may continue to light, if the outer glass is damaged, immediately discontinue use. Since the inner capsule operates at high temperature and pressure and could unexpectedly shatter, thereby creating a risk of person injury or property damage. Do not use lamp in close proximity to combustible materials or those adversely affected by drying or fading action because of heat radiation in the beam.

Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

November 27, 2015