



FlexLED LED modules produce an exceptional combination of performance and light quality from its compact design, producing up to 1 000 lumens of brilliant white light while consuming a maximum of 14.7 watts.

The light engine exceeds ENERGY STAR® requirements and is certified to the high efficacy standards of California Title 24, including CRIs above 94.

- ▶ High quality die cast aluminum housing
- ▶ Variety of colour temperatures
- ▶ Quick and tool-less twist and lock installation
- ▶ Flexible design that mounts into a variety of trims and housings



Order code	Description	Watts (W)	Volts (VAC)	Colour Temp. (K)	CRI	Average Life (L70)	Lumens (lm)	Beam Angle ¹ (°)	Dimmable (Y/N)	Case qty
63221	LED/MOD/11.8W/27K/STD	11.8	120	2 700	96	50 000	750	88	Y	48
63222	LED/MOD/11.8W/30K/STD	11.8	120	3 000	95	50 000	750	88	Y	48
63223	LED/MOD/11.8W/40K/STD	11.8	120	4 000	95	50 000	750	88	Y	48
63224	LED/MOD/14.7W/27K/STD	14.7	120	2 700	95	50 000	1 000	88	Y	48
63225	LED/MOD/14.7W/30K/STD	14.7	120	3 000	96	50 000	1 000	88	Y	48
63226	LED/MOD/14.7W/40K/STD	14.7	120	4 000	94	50 000	1 000	88	Y	48



¹ Depending on trim. See IES for exact value.

Modules