




GLIMPSE

FEATURES

- Provides up to 20 % more light than similar competitor offerings
- Can be retrofit into most 4", 5" or 6" recessed downlights or surface mounted for new construction applications
- Designed for a 50 000 hour life
- Dimmable to 5 %
- Available in 2 700, 3 000 or 4 000 K
- Environmentally friendly- contains no mercury or other hazardous materials
- IC rated when used in an approved IC rated recessed can
-  Visit our website for a complete listing of all DEFINITY ENERGY STAR qualified products

DL6 { MOL = 2 5/8 in. (59 mm)
Dia. = 7 1/2 in. (186.5 mm)

DL4 { MOL = 2 1/2 in. (53.5 mm)
Dia. = 5 1/2 in. (139.5 mm)

CERTIFICATIONS



Order code	Description	Watts (W)	Base	Volts (VAC)	Colour temp. (K)	CRI	Average life (hrs)	Initial lumens (lm)	Case qty	Incandescent equivalent (W)	Dimmable (Yes/No)
GLIMPSE 6"											
62949	LS GLP6 W27 120 WH S1 BX	13	E26	120	2 700	80	50 000	725	6	65	Y
62950	LS GLP6 WW 120 WH S1 BX	13	E26	120	3 000	80	50 000	750	6	65	Y
62951	LS GLP6 NW 120 WH S1 BX	13	E26	120	4 000	80	50 000	775	6	65	Y
GLIMPSE 4"											
62944	LS GLP4 W27 120 WH S1 BX	9	E26	120	2 700	80	40 000	525	6	50	Y
62945	LS GLP4 WW 120 WH S1 BX	9	E26	120	3 000	80	40 000	550	6	50	Y
62946	LS GLP4 NW 120 WH S1 BX	9	E26	120	4 000	80	40 000	575	6	50	Y

PRODUCT DESCRIPTION GUIDE

Family	Product	Colour temperature	Voltage	Finish
	GLP6 6" Downlight	W27 Warm White 2 700 K	120 120 Volt	WH White
	GLP4 4" Downlight	WW Warm White 3 000 K		
		NW Neutral White 4 000 K		

¹ Life rating based on L70 lumen depreciation design criteria. Average life of lamps that have been approved for ENERGY STAR early submission or complete submission can vary.