## Technical Information Bulletin

# **LED Outdoor Luminaires**

### ORDERING INFORMATION

Order code: 63774

**Description:** LED/WP/18W/40K/120V/BRZ/PC/STD

UPC: 69549637740

Case quantity: 12



### **FEATURES AND SPECIFICATIONS**

Dusk to dawn photocell included automatically controlling when the light is turned on and off. IP65 - suitable for wet locations that receive direct contact with rain, snow or other moisture. Driver reliability in the coldest of temperatures (starting temperature rated to -30° C) High quality LÉD chips ensure total efficiency

Heat sink material: Diecast aluminum Lens material: Polycarbonate

- 30 °C / - 22 °F to 40 °C / 104 °F Operating temperature:

CAN ICES-005 (B) - This lighting equipment complies with Canadian standard ICES-005 for use in residential applications.













### FIXTURE PERFORMANCE

Wattage (W): 18 Input Voltage (V): 120 Color temperature (K): 4 000 Lumens (lm): 1 746 Efficacy(LPW): 97 CRI: 83 L70 hours: 50 000 IP rating: 65 Surge protection (kV): 10 Housing finish: **Bronze** Photocell included: Yes



### Technical Information Bulletin

### LED Outdoor Luminaires

#### ORDERING INFORMATION

Order code: 63774

**Description:** LED/WP/18W/40K/120V/BRZ/PC/STD


**UPC**: 69549637740


Case quantity: 12

### **DIMENSIONS**

Length: 6 11/32" (16.14 cm)
Width: 3 1/32" (7.72 cm)
Height: 8 1/4" (20.96 cm)

### **TECHNICAL DRAWINGS**





#### WARNINGS

- Installation and maintenance must be performed by licensed electricians only.
- To avoid risk of electric shock, make sure to turn off main power switch prior to installation or maintenance.
- Must be installed in compliance with Canadian Electrical Code in Canada or National Electrical Code (NEC) in the US.
- Make sure input voltage and frequency are compatible with the fixture. Check installation guide for power requirements prior to installation.
- This product use an input 100-277 VAC driver, the actual working voltage is dependent on the input voltage of the photocell that is installed on the product (where applicable).

