


Date: _____
 In hands date of project: _____
 Project name/Number: _____
 Name of distributor: _____
 Client #: _____
 Name of end user: _____



ORDERING INFORMATION

Order code: 64008
 Description: LED/MR16/6.5W/30K/38/STD
 UPC: 69549640085
 Case quantity: 24

PERFORMANCE DATA

Shape: MR16
 Base: GU5.3
 Wattage (W): 6.5
 Lamp voltage (VAC): 12
 Colour temperature (K)**: 3 000
 Average life (L70 hours): 40 000
 Initial lumens (lm)*: 595
 Initial lumens per watt (lm/W): 91
 CRI: 83
 R9: 13
 Beam angle (°): 38
 CBCP: 1 213
 Power factor: 0.80
 Operating temperature range: - 40 °C / - 40 °F to 40 °C / 104 °F

*Initial lumens range: +/- 10 %

**Typical colour temperature range: +/- 10 %



CAUTIONS

- Turn power off before inspection, installation, or removal.
- Risk of electrical shock – do not use where directly exposed to water or weather.
- Not for use in totally enclosed luminaires.
- Suitable for use in damp locations.
- Do not open – no user serviceable parts inside.
- Use only on 120 VAC, 60Hz circuits.
- This device is not intended for use with emergency exit fixtures or emergency exit lights.
- Compatible with most dimmers.
- For complete dimmer and warranty information visit www.standardpro.com.
- Not recommended for use with timers.
- Operating temperature: -40 °C / -40 °F to 40 °C / 104 °F
- 5 Years Limited Warranty.

Qty	Description	Price

I accept the specifications of the lamp configuration mentioned above.

Name: _____
 Company: _____
 Signature: _____

Date: _____

Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

COMPATIBLE DIMMER/TRANSFORMER LIST

Dimmers	Transformers
Cooper: SAL06P	Contrast Lighting: MLV-EC50M (Magnetic)
Cooper: AAL06	Contrast Lighting: MLV-EC50M (Magnetic) TDC Power Products: DA-50-12TH5 (Magnetic)
Leviton: DSM10-1LZ	Contrast Lighting: MLV-EC50M (Magnetic) TDC Power Products: DA-50-12TH5 (Magnetic)
Lutron: DVLV600HP	Contrast Lighting: MLV-EC50M (Magnetic)