

Date: _____
 In hands date of project: _____
 Project name/Number: _____
 Name of distributor: _____
 Client #: _____
 Name of end user: _____

ORDERING INFORMATION

Order code: 63955
 Description: LED/P20/7W/30K/40/STD
 UPC: 69549639553
 Case quantity: 12

PERFORMANCE DATA

Shape: PAR20
 Base: E26
 Wattage (W): 7
 Lamp voltage (VAC): 120
 Colour temperature (K)**: 3 000
 Average life (L70 hours): 40 000
 Initial lumens (lm)*: 502
 Initial lumens per watt (lm/W): 72
 CRI: 93
 R9: 66
 Beam angle: 40
 CBCP: 918
 Power factor: 0.93
 Operating temperature range: - 40 °C / - 40 °F to 40 °C / 104 °F

*Initial lumens range: +/- 10 %

**Typical colour temperature range: +/- 10 %



CAUTIONS

- Turn power off before inspection, installation, or removal.
- Risk of electrical shock – do not use where directly exposed to water or weather.
- Not for use in totally enclosed luminaires.
- Suitable for use in damp locations.
- Do not open – no user serviceable parts inside.
- Added weight of the device may cause instability of a freestanding portable luminaire. Use in portable table lamps in which the distance from the bottom of the base to the top of the lamp holder does not exceed three (3) times the minimum base diameter.
- Use only on 120 VAC, 60Hz circuits.
- This device is not intended for use with emergency exit fixtures or emergency exit lights.
- Compatible with most dimmers.
- For complete dimmer and warranty information visit www.standardpro.com.
- Not recommended for use with timers.

Qty	Description	Price


I accept the specifications of the lamp configuration mentioned above.

Name: _____
 Company: _____
 Signature: _____

Date: _____

Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

March 14, 2016



COMPATIBLE DIMMER LIST

Legrand	HCL453P
Cooper	SAL06P, SLC03P, AAL06
Leviton	IPL06, 6674
Lutron	DVCL-153P, CTCL-153P, MACL-153P, AYCL-253P, DVCL-253P, DVELV-300P, SELV-300P