


Date: _____
 In hands date of project: _____
 Project name/Number: _____
 Name of distributor: _____
 Client #: _____
 Name of end user: _____



MOL : 4 ²⁵/₃₂ in. (118 mm) Dia. : ²⁹/₃₂ in. (23 mm)

ORDERING INFORMATION

Order code: 64467
 Description: LED/R7S/8W/30K/118/ND/STD
 UPC: 69549644670
 Case quantity: 200

PERFORMANCE DATA

Shape: Tube
 Base: R7S
 Wattage (W): 8
 Lamp voltage (VAC): 120
 Colour temperature (K)**: 3 000
 Average life (L70 hours): 15 000
 Initial lumens (lm)*: 650
 Initial lumens per watt (lm/W): 81
 CRI: 80
 Beam angle: 360
 Power factor: 0.6
 Operating temperature range: - 10 °C / 14 °F to 40 °C / 104 °F

*Initial lumens range: +/- 10 % **Typical colour temperature range: +/- 5 %



CAUTIONS

- Risk of electrical shock – Suitable for use in dry location.
- Not for use in totally enclosed luminaires.
- This device is not intended for use with emergency exit fixtures or lights.
- Not for use with dimmers
- For complete warranty information visit www.standardpro.com.
- Operating temperature: -10°C / 14°F to 40°C / 104°F.
- 2 Years Limited Warranty.

Qty	Description	Price

I accept the specifications of the lamp configuration mentioned above.

Name: _____
 Company: _____
 Signature: _____

Date: _____

Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.