



The perfect replacement for traditional lamps, E-LUME LED lamps offer good value with great performance while providing bright clean light and consistent colour from lamp to lamp.

LED Lamps



Order code	Description	Watts (W)	Base	Volts (VAC)	Colour temp. (K)	CRI	Average life ¹ (hrs)	Initial lumens ² (lm)	Beam angle (°)	CBCP (cd)	Traditional equivalent (W)	Dimmable ³ (Yes/No)	Case qty
MR16 - GU5.3													
MOL : 2 3/4 in. (57 mm) Dia. : 1 33/32 in. (50 mm)													
63605	LED/MR16/7W/30K/25/ELUME	7	GU5.3	12	3 000	80	40 000	520	25	2 000	50	Y	48
63606	LED/MR16/7W/30K/40/ELUME	7	GU5.3	12	3 000	80	40 000	520	40	1 100	50	Y	48
GU10 - All Glass⁴													
MOL : 2 3/16 in. (55 mm) Dia. : 1 33/32 in. (50 mm)													
65394	LED/GU10/5W/30K/40/GLASS/ELUME	5	GU10	120	3 000	82	25 000	544	40	967	50	Y	100
65400	LED/GU10/5W/40K/40/GLASS/ELUME	5	GU10	120	4 000	83	25 000	538	40	965	50	Y	100
GU10													
MOL : 2 3/16 in. (55 mm) Dia. : 1 33/32 in. (50 mm)													
63609	LED/GU10/7W/30K/25/GRY/ELUME	7	GU10	120	3 000	80	40 000	520	25	2 000	50	Y	48
GU10*													
MOL : 2 3/32 in. (53.5 mm) Dia. : 1 13/16 in. (49 mm)													
64634	LED/GU10/7W/30K/25/ELUME	7	GU10	120	3 000	84	25 000	563	25	2450	50	Y	48
64635	LED/GU10/7W/30K/25/GRY/ELUME	7	GU10	120	3 000	84	25 000	563	25	2450	50	Y	48
64636	LED/GU10/7W/30K/35/ELUME	7	GU10	120	3 000	84	25 000	553	35	1375	50	Y	48
MR16 - E26													
MOL : 2 3/32 in. (53 mm) Dia. : 1 33/32 in. (50 mm)													
63854	LED/MR16E26/7W/30K/35/ELUME	7	E26	120	3 000	80	30 000	500	35	1 106	50	Y	48
64542	LED/MR16E26/7W/40K/35/ELUME	7	E26	120	4 000	80	30 000	525	35	1 150	50	Y	48
Omni⁴													
5.5 W - MOL : 3 29/32 in. (99 mm) Dia. : 2 5/32 in. (55 mm)													
9.5 W - MOL : 4 13/32 in. (112 mm) Dia. : 2 3/8 in. (60 mm)													
64403	LED/OMNI/5.5W/27K/ND/ELUME	5.5	E26	120	2 700	80	15 000	450	150	N/A	40	N	12
64404	LED/OMNI/5.5W/30K/ND/ELUME	5.5	E26	120	3 000	80	15 000	450	150	N/A	40	N	12
64407	LED/OMNI/9.5W/27K/ND/ELUME	9.5	E26	120	2 700	80	15 000	750	140	N/A	60	N	12
64408	LED/OMNI/9.5W/30K/ND/ELUME	9.5	E26	120	3 000	80	15 000	750	140	N/A	60	N	12
Omni 4 pack⁴													
MOL : 4 13/32 in. (112 mm) Dia. : 2 3/8 in. (60 mm)													
64931	LED/OMNI/9.5W/27K/ND/ELUME 4P	9.5	E26	120	2 700	80	15 000	750	140	N/A	60	N	12
64932	LED/OMNI/9.5W/30K/ND/ELUME 4P	9.5	E26	120	3 000	80	15 000	750	140	N/A	60	N	12
64970	LED/OMNI/9.5W/40K/ND/ELUME 4P	9.5	E26	120	4 000	80	15 000	750	140	N/A	60	N	12
64971	LED/OMNI/9.5W/50K/ND/ELUME 4P	9.5	E26	120	5 000	80	15 000	750	140	N/A	60	N	12



¹ Life rating based on L70 lumen depreciation design criteria. Average life of lamps that have been approved for ENERGY STAR early submission or complete submission can vary. ENERGY STAR early submission dictates that manufacturers can only claim 25 000 hour life with 3 000 hour actual life test data, 6 000 hour LM-80 data and in-situ temperature measurements. Once a product has been fully qualified, manufacturers may increase the lifetime of a product by demonstrating full compliance with the ENERGY STAR criteria at the new lifetime with Lumen Maintenance at the minimum required test period.

² Typical lumens +/- 10%

³ For a complete list of compatible dimmers and ENERGY STAR qualified products, please visit www.standardpro.com

⁴ Not ENERGY STAR certified.