



Pulse Start

Applications

- Highbay industrial
- Manufacturing lighting
- Site lighting
- Big box retail
- Convention centers
- Indoor sports/recreation

ED28



Dia. = 3 1/2 in. (89 mm)
MOL = 8 3/8 in. (211 mm)
LCL = 5 in. (127 mm)

ED28



Dia. = 3 1/2 in. (89 mm)
MOL = 8 3/8 in. (211 mm)
LCL = 5 in. (127 mm)

ED37



Dia. = 4 3/4 in. (117.5 mm)
MOL = 11 1/2 in. (292 mm)
LCL = 7 in. (178 mm)

ED37



Dia. = 4 3/4 in. (117.5 mm)
MOL = 11 1/2 in. (292 mm)
LCL = 7 in. (178 mm)

ED37



Dia. = 4 3/4 in. (117.5 mm)
MOL = 11 1/2 in. (292 mm)
LCL = 7 in. (178 mm)

ED37



Dia. = 4 3/4 in. (117.5 mm)
MOL = 11 1/2 in. (292 mm)
LCL = 7 in. (178 mm)

O = Open rated for indoor fixtures E = Enclosed rated

Order code	Description	Shape	Base	ANSI code	Colour temp. (K)	CRI	Average life (hrs)	Initial lumens (lm)	Mean lumens (lm)	Burn pos.	Finish	Luminaire	Case qty	Figure
400 watts														
58001	MS400W/V/ED28/PS/740 STD	ED28	E39	M155/E	4 000	65	20 000	44 000	35 200	BU±15°	Clear	E	12	E
58036	MP400W/V/ED28/UVS/PS/740 STD	ED28	EX39	M155/O	4 000	68	20 000	41 000	35 000	BU±15°	Clear	O	12	H
58064	MS400W/H75/ED28/PS/740 STD	ED28	E39	M155/E	4 000	65	10 000	40 000	32 000	HOR±75°	Clear	E	12	E
57994	MS400W/V/PS/740 STD	ED37	E39	M155/E	4 000	68	20 000	44 000	35 000	BU±15°	Clear	E	6	I
58066	MS400W/C/V/PS/737 STD	ED37	E39	M155/E	3 700	70	20 000	42 000	33 600	BU±15°	Coated	E	6	K
57968	MS400W/H75/PS/740 STD	ED37	E39	M155/E	4 000	68	26 000	40 000	32 000	HOR±75°	Clear	E	6	I
57991	MP400W/V/UVS/PS/740 STD	ED37	EX39	M155/O	4 000	68	20 000	41 000	33 000	BU±15°	Clear	O	6	L
58070	MP400W/C/V/UVS/PS/737 STD	ED37	EX39	M155/O	3 700	70	20 000	39 000	31 000	BU±15°	Coated	O	6	J
450 watts														
59140	MS450W/V/PS/740 STD	ED37	E39	M155/E	4 000	65	20 000	50 000	40 000	BU±15°	Clear	E	6	I
57981	MP450W/BU/UVS/PS/740 STD	ED37	EX39	M155/O	4 000	65	20 000	47 000	37 600	BU±15°	Clear	O	6	L
57974	MP450W/C/BU/UVS/PS/737 STD	ED37	EX39	M155/O	3 700	70	20 000	45 000	36 000	BU±15°	Coated	O	6	J
1 000 watts														
61055	MS1000W/BU/ED37/PS/740 STD	ED37	E39	M141/E	4 000	68	12 000	115 000	86 000	BU±15°	Clear	E	6	I