

Lamps pertaining to this category have line voltage compatibility and are used in general residential and commercial applications. Their special feature is to produce directional light.

Order code	Description	Watts (W)	Base	Volts (V)	Finish/Colour	Average life at 120 V (hrs)	Filament	Lumens at 120 V (lm)	Case qty
BR25									
MOL : 4 ²⁵ / ₃₂ in. (118 mm) LCL : 3 ²⁵ / ₃₂ in. (85 mm)									
¹ 50121	100BR25/SP/5M/130V/STD	100	E26	130	Clear	5 000	C-9	770	100
BR30									
MOL : 5 ¹ / ₈ in. (130 mm) LCL : 3 ²⁵ / ₃₂ in. (85 mm)									
¹ 50219	50BR30/FL/5M/130V/STD	50	E26	130	Clear	5 000	C-9	240	60
¹ 50220	60BR30/FL/5M/130V/STD	60	E26	130	Clear	5 000	C-9	320	60
50077	65BR30/FL/5M/ES/130V/STD	65	E26	130	Clear	5 000	CC-6	470	60
50079	65BR30/SP/5M/ES/130V/STD	65	E26	130	Clear	5 000	CC-6	470	60
BR38									
MOL : 5 ²⁵ / ₃₂ in. (147 mm) LCL : 3 ³ / ₃₂ in. (83 mm)									
¹ 50056	75BR38/SP/5M/130V/STD	75	E26	130	Clear	5 000	C-9	580	12
¹ 52001	120BR38/FL/5M/ES/130V/STD	120	E26	130	Clear	5 000	CC-6	895	12
BR40									
MOL : 6 ³ / ₁₆ in. (167 mm) LCL : 4 ¹ / ₄ in. (108 mm)									
¹ 50080	65BR40/FL/5M/ES/130V/STD	65	E26	130	Clear	5 000	CC-6	470	12
R14									
MOL : 2 ¹ / ₈ in. (54 mm) LCL : 1 ²⁵ / ₃₂ in. (42 mm)									
50665	25R14/FL/1.5M/120V/STD	25	E26	120	Clear	1 500	CC-2V	150	120
50663	40R14/CL/FL/1.5M/120V/STD	40	E26	120	Clear	1 500	CC-2V	280	120
MOL : 2 ⁹ / ₁₆ in. (65 mm) LCL : 1 ²⁵ / ₃₂ in. (50 mm)									
50666	25R14/FL/1.5M/E17/120V/STD	25	E17	120	Clear	1 500	CC-2V	150	120
R16									
MOL : 3 ¹ / ₂ in. (89 mm)									
52168	25R16/SF/1.5M/E12/130V/STD	25	E12	130	Frost	3 000	CC-2V	120	500
50134	40R16/SW/1M/120V/STD	40	E26	120	Soft white	1 000	CC-6	470	100
50135	60R16/SW/1M/125 130V/STD	60	E26	125-130	Soft white	2 500	CC-6	310	100
R19									
MOL : 3 ²⁵ / ₃₂ in. (101 mm) LCL : 3 ¹ / ₃₂ in. (77 mm)									
50136	40R19/SW/1.5M/120V/STD	40	E26	120	Soft white	1 500	CC-6	320	60
¹ 50138	75R19/SW/1.5M/120V/STD	75	E26	120	Soft white	1 500	CC-6	770	200
R20									
MOL : 3 ²⁵ / ₃₂ in. (99 mm) LCL : 2 ¹⁵ / ₁₆ in. (75 mm)									
50211	30R20/SP/5M/130V/STD	30	E26	130	Clear	5 000	C-9	145	60
50215	30R20/FL/5M/130V/STD	30	E26	130	Frost	5 000	C-9	130	60
61703	45R20/FL/5M/130V/STD	45	E26	130	Frost	5 000	CC-6	255	60
61705	45R20/SP/5M/130V/STD	45	E26	130	Frost	5 000	CC-6	255	60
¹ 50217	75R20/FL/5M/130V/STD	75	E26	130	Clear	5 000	C-9/5	410	60
¹ 50213	75R20/SP/5M/130V/STD	75	E26	130	Clear	5 000	CC-6	575	200

¹ This product is no longer manufactured as per Energy Efficiency Regulations, note that it will remain available until stock is depleted.

General Service Reflectors