

## ORDERING INFORMATION



Order code: 63299  
 Description: LED/CL11/15W/40K/FM/RND/STD  
 UPC: 69549632998  
 Case quantity: 1  
 Luminaire description: Round LED Ceiling Luminaire

## FEATURES AND SPECIFICATIONS

**Lens type:** Frosted Acrylic Diffuser  
**Lens benefits:** Easy to install twist and lock diffuser  
**Housing:** Simple, functional and low profile design.  
**Applications:** Ideal for use in closets, utility areas, hallways, bedrooms, offices & various residential and commercial applications.  
**Benefits compared to Traditional Light:** Uses less energy than fluorescent lights, lasts longer and is maintenance free.



For a complete list of ENERGY STAR qualified products, please visit [www.standardpro.com](http://www.standardpro.com)

## FIXTURE PERFORMANCE

Wattage (W): 15  
 Colour temperature (K): 4 000  
 CRI: 80  
 Average life in hours: 50 000  
 Lumens: 1 000  
 Efficacy with lens (LPW): 67  
 Voltage (V): 120  
 Hertz (Hz): 60  
 mili Amps (mA): 340  
 Beam angle: 90°  
 Mounting: Surface Mount/Flush-mount

## POWER FACTOR (PF)

0.95

## TOTAL HARMONIC DISTORTION (THD)

< 20 %

## AMBIENT OPERATING TEMPERATURES

-10°C/44°F to 40°C/104°F


## COMPATIBLE DIMMER LIST

COOPER: DAL06P, SAL06P and SLC03P  
 LEVITON: Decora – 6674 and Illuma Tech IPL06  
 LUTRON: Maestro MACL-153P, Diva DVCL-153P, Contour CTCL-153P


## ORDERING INFORMATION

Order code: 63299  
 Description: LED/CL11/15W/40K/FM/RND/STD  
 UPC: 69549632998  
 Case quantity: 1  
 Luminaire description: Round LED Ceiling Luminaire

## PHOTOMETRICS - BEAM SPREAD\*



## PHOTOMETRICS - CANDELA DISTRIBUTION\*



## PHOTOMETRICS - COEFFICIENTS OF UTILIZATION (ZONAL CAVITY METHOD)\*

RCC %:	80				70				50				30				10				0
RW %:	70	50	30	0	70	50	30	0	50	30	20	0	50	30	20	0	50	30	20	0	0
RCR: 0	1.17	1.17	1.17	1.17	1.13	1.13	1.13	.90	1.05	1.05	1.05	.99	.99	.99	.99	.93	.93	.93	.93	.90	.90
1	1.04	.98	.93	.88	1.00	.95	.90	.71	.88	.84	.81	.83	.79	.77	.77	.75	.75	.72	.72	.70	.70
2	.93	.84	.76	.70	.90	.81	.74	.58	.76	.70	.65	.71	.66	.62	.62	.59	.59	.56	.56	.56	.56
3	.85	.73	.64	.57	.81	.71	.62	.48	.66	.59	.54	.62	.56	.51	.51	.49	.49	.46	.46	.46	.46
4	.77	.64	.55	.48	.74	.62	.54	.41	.58	.51	.45	.55	.48	.43	.43	.42	.42	.39	.39	.39	.39
5	.71	.57	.48	.41	.68	.56	.47	.35	.52	.45	.39	.49	.42	.37	.37	.36	.36	.33	.33	.33	.33
6	.65	.51	.42	.35	.63	.50	.41	.31	.47	.39	.34	.44	.38	.33	.33	.32	.32	.29	.29	.29	.29
7	.60	.46	.37	.31	.58	.45	.37	.27	.43	.35	.30	.40	.34	.29	.29	.28	.28	.25	.25	.25	.25
8	.56	.42	.34	.28	.54	.41	.33	.24	.39	.32	.26	.37	.30	.26	.26	.25	.25	.22	.22	.22	.22
9	.52	.39	.30	.25	.51	.38	.30	.22	.36	.29	.24	.34	.28	.23	.23	.22	.22	.19	.19	.19	.19
10	.49	.36	.28	.22	.47	.35	.27	.20	.33	.26	.21	.31	.25	.21	.21	.20	.20	.17	.17	.17	.17

\*Complete IES information available at [www.standardpro.com](http://www.standardpro.com)


## ORDERING INFORMATION

Order code: 63299  
 Description: LED/CL11/15W/40K/FM/RND/STD  
 UPC: 69549632998  
 Case quantity: 1  
 Luminaire description: Round LED Ceiling Luminaire

## DIMENSIONS

Length: 11" (27.94 cm)  
 Diameter: 11" (27.94 cm)  
 Width: -  
 Depth: 3.5" (8.89 cm)

## TECHNICAL DRAWINGS



## WARNINGS

- Installation and maintenance must be performed by licensed electricians only.
- To avoid risk of electric shock, make sure to turn off main power switch prior to installation or maintenance.
- Must be installed in compliance with Canadian Electrical Code in Canada or National Electrical Code (NEC) in the US.
- Make sure input voltage and frequency are compatible with the fixture. Check installation guide for power requirements prior to installation.

**WARNING – Risk of electric shock. Suitable for damp locations.**