



AMBIANCE AMBER lamps deliver warm lighting creating a comfortable and cozy atmosphere.

These lamps offer style while minimizing energy and maintenance costs compared to incandescent equivalents. Completely dimmable, they allow the user to create a desired mood for any occasion.

Perfect for restaurants, lounges, spas and patios.



Amber Ambiance



AMBIANCE A M B R E

Order code	Description	Watts (W)	Base	Volts (VAC)	Average life (hrs)	Initial lumens ¹ (lm)	Beam angle (°)	Traditional equivalent (W)	Dimmable ² (Yes/No)	Case qty
MR16 MOL : 1 29/32 in. (47 mm) Dia. : 1 31/32 in. (50 mm)										
62891	LED/MR16/7W/FL/12V/40/D/STD/GRY/AMB	7	GU5.3	12	25 000	470	40	35	Y	48
MR16 - GU10 MOL : 2 3/32 in. (55 mm) Dia. : 1 31/32 in. (50 mm)										
63229	LED/GU10/7W/FL/40/D/STD/GRY/AMB	7	GU10	120	25 000	470	40	35	Y	48
B11 MOL : 3 29/32 in. (96 mm) Dia. : 1 3/8 in. (35 mm)										
63574	LED/B11/5W/D/STD/WH/AMB	5	E12	120	25 000	280	117	40	Y	48
PAR20 MOL : 3 7/32 in. (82 mm) Dia. : 2 39/32 in. (63 mm)										
62892	LED/PAR20/7W/FL/40/D/STD/GRY/AMB	7	E26	120	25 000	380	40	35	Y	48
PAR30LN MOL : 4 3/16 in. (116 mm) Dia. : 3 3/4 in. (95 mm)										
62893	LED/PAR30LN/11W/FL/40/D/STD/GRY/AMB	11	E26	120	25 000	680	40	50	Y	24
PAR38 MOL : 5 5/32 in. (131 mm) Dia. : 4 3/4 in. (121 mm)										
62894	LED/PAR38/17W/FL/40/D/STD/GRY/AMB	17	E26	120	25 000	1080	40	90	Y	24
A19 Omni MOL : 4 29/32 in. (118 mm) Dia. : 2 3/8 in. (60 mm)										
62895	LED/OMNI/10W/D/STD/GRY/AMB	10	E26	120	25 000	750	215	60	Y	48
BR30 MOL : 5 5/32 in. (131 mm) Dia. : 3 3/4 in. (95 mm)										
62896	LED/BR30/10W/D/STD/GRY/AMB	10	E26	120	25 000	700	108	65	Y	24

¹ Typical lumens +/- 5 %
² For a complete list of compatible dimmers and ENERGY STAR qualified products, please visit www.standardpro.com

