

ИOL

ORDERING INFORMATION

Order code:	63950
Description:	LED/P20/7W/27K/25/STD
UPC:	69549639508
Case quantity:	12

PERFORMANCE DATA

Shape:	PAR20
Base:	E26
Wattage (W):	7
Lamp voltage (VAC):	120
Colour temperature (K)**:	2 700
Average life (L70 hours):	40 000
Initial lumens (lm)*:	509
Initial lumens per watt (lm/W):	73
CRI:	92
R9:	55
Beam angle (°):	25
CBCP:	1 497
Power factor:	0.93
Operating temperature range:	- 40 °C / - 40 °F to 40 °C / 104 °F

*Initial lumens range: +/- 10 % **Typical colour temperature range: +/- 10 %



CAUTIONS

- Turn power off before inspection, installation, or removal.
- Risk of electrical shock do not use where directly exposed to water or weather.
- Not for use in totally enclosed luminaires.Suitable for use in damp locations.
- Do not open no user serviceable parts inside.
- Added weight of the device may cause instability of a freestanding portable luminaire. Use in portable table lamps in which the distance from the bottom of the base to the top of the lamp holder does not exceed three (3) times the minimum base diameter. • Use only on 120 VAC, 60Hz circuits.
- . This device is not intended for use with emergency exit fixtures or emergency exit lights.
- Compatible with most dimmers.
- · For complete dimmer and warranty information visit www.standardpro.com.
- Not recommended for use with timers.

Qty	Description	Price

I accept the specifications of the lamp configuration mentioned above.

Name:	
Company:	
Signature:	Dat
Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.	

e:

Diameter

MOL : 3 11/32 in. (85 mm)

Dia.: 2 15/32 in. (63 mm)

COMPATIBLE DIMMER LIST

Legrand	HCL453P
Cooper	SAL06P, SLC03P, AAL06
Leviton	IPL06, 6674
Lutron	DVCL-153P, CTCL-153P, MACL-153P, AYCL-
	253P, DVCL-253P, DVELV-300P, SELV-300P

STANDARD®