



4 1/4" Housings

Order code	Description	Opening diameter (in.)	Volts (V)	Socket	Case qty
------------	-------------	------------------------	-----------	--------	----------

Remodeler - IC** Airtight

64359	RF4in/REMOD/IC/LED/E26/ELUME	4 1/4	120	E26	6
64360	RF4in/REMOD/IC/LED/GU10/ELUME	4 1/4	120	GU10	6

New Construction - IC** Airtight

64361	RF4in/NC/IC/NOBOX/LED/GU10/ELUME	4 1/4	120	GU10	6
64362	RF4in/NC/IC/NOBOX/LED/E26/ELUME	4 1/4	120	E26	6

New Construction - IC Airtight

64363 ¹	RF4in/NC/IC/E26/ELUME	4 1/4	120	E26	6
64364 ¹	RF4in/NC/IC/GU10/ELUME	4 1/4	120	GU10	6

4 1/4" Trims - MR16 (GU10 & E26) & PAR16

Side view



Order code	Description	Colour	Rotation angle (°)	Case qty
------------	-------------	--------	--------------------	----------

Deep Baffle - Gimbal

Shape: Round Aperture: Round
Dia. : 4 in. (101.6 mm)

64370	RF4/TRIM/GMB.DB/BLK/MR16/ELUME	Black	30	24
64371	RF4/TRIM/GMB.DB/BLK_BR.NKL/MR16/ELUME	Black / Brushed Nickel	30	24
64375	RF4/TRIM/GMB.DB/WH/MR16/ELUME	White	30	24

Gimbal

Shape: Round Aperture: Round
Dia. : 4 in. (101.6 mm)

64380	RF4/TRIM/GMB/BR.NKL/MR16/ELUME	Brushed Nickel	30	12
64382	RF4/TRIM/GMB/WH/MR16/ELUME	White	30	12
64385	RF4/TRIM/GMB/BRZ/MR16/ELUME	Bronze	30	12

Reflector - Gimbal

Shape: Round Aperture: Round
Dia. : 4 in. (101.6 mm)

65548	RF4/TRIM/GMB.DB/RFL_WH/MR16/ELUME	Chrome / White	30	24
-------	-----------------------------------	----------------	----	----

Compatible Lamps

MR16 (GU10)

MR16 (E26)

PAR16 (E26)



*For complete warranty information please visit www.standardpro.com

**Only valid with LED lamps

Recessed Fixtures