Technical Information Bulletin

LED Linear

Dia.: 1 in. (26 mm)

Date:	
In hands date of project:	
Project name/Number:	
Name of distributor:	
Client #:	
Name of end user:	



Nominal length: 24 in. (610 mm)

ORDERING INFORMATION

Order code: 65473

Description: LED/T8/S4/9W/840/24/STD

UPC: 69549654730

Case quantity: 25

PERFORMANCE DATA

Shape: T8 Base: G13

Starting method: Instant, Rapid & Program Start

Lamp voltage (VAC): 120 V - 277 V / 347 V

 Color temperature (K)**:
 4 000

 Average life (L70 hours):
 50 000

 CRI:
 >80

 Beam angle (°):
 >240

Operating temperature range: -20°C / -4°F to 45°C / 113°F

DLC Standard
*Initial lumens range: +/- 10 %
**Typical colour temperature range: +/- 5 %

Order code	Average System Watts (W)			Initial Lumens (lm)*		
	LBF	NBF	HBF	LBF	NBF	НВБ
65473	10	12	16	1 100	1 350	1 800











CAUTIONS

THIS LAMP OPERATES ON INSTANT START, RAPID START AND MANY PROGRAM START ELECTRONIC BALLASTS.

Direct replacement for 17 watts lamps only. Risk of fire. Do not install this lamp in a pre-heat luminaire. Risk of electric shock – for use in damp locations.

Description	Price	Price		
cations of the lamp configuration mentione	d above.			
	Date:			
	•	cations of the lamp configuration mentioned above.		

Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

