

SBS Fast-Acting Ferrule Fuses

Unique dimensions for today's smaller equipment and components. Fast-acting general purpose fuse developed in response to the industry's demand for smaller equipment and components. The only fuse in their size with a full 600 VAC rating for all ampere ratings by UL standard 248-14 and CSA No. 59.2, and are the only fuses of this size with an interrupting rating of 100kA RMS. SBS fuses are 1-3/8" long, smaller by 1/8" than most standard midget fuses and are available in 22 ampere ratings, from 2/10A to 30A. (Not for Branch Circuit Protection).

Features/Benefits:

- Small unique physical size for maximum design flexibility and non-interchangeability with other fuse classes
- Fiberglass body provides dimensional stability in harsh industrial environments
- Can be used with UltraSafe™ fuse holder
- 1 3/8" x 13/32" dimensions

Highlights:

- Fast-acting
- Unique dimensions

Applications:

- Control circuits
- Lighting ballasts
- Meter circuits
- Electronic circuits
- General purpose protection

Catalog Numbers (amps)

SBS2/10	SBS1-8/10	SBS10
SBS4/10	SBS2	SBS12
SBS1/2	SBS3	SBS15
SBS3/4	SBS4	SBS20
SBS8/10	SBS5	SBS25
SBS1	SBS6	SBS30
SBS1-1/2	SBS7	
SBS1-6/10	SBS8	

Cross Reference:

SBS will replace Bussmann BBS, Littelfuse BLS fuses



Ratings:

Volts : 600VAC
Amps : 2/10 to 30A
I.R. : 100kA I.R.

Approvals:

- UL Listed to standard 248-14 File E33925
- CSA Certified to Standard C22.2 No. 248.14

