


# Galvanized Ground Rod, Pointed – 813400



- Meets ANSI®/NEMA® GR1
- Zinc-coated exteriors are hot-dip galvanized for solid protection against corrosion, in accordance with ASTM® specification A153-78
- Surfaces are rigidly inspected to eliminate seams, slivers and other defects



<b>Part Number</b>	<b>813400</b>
Material	Steel
Finish	Hot-Dip Galvanized
Tensile Strength	552 MPa Min
Ground Rod Diameter, Nominal	3/4"
Ground Rod Diameter, Actual (Ø)	18.5 mm
Length (L)	3 m
Unit Weight	6.3 kg
UPC Label	No
Certifications	CSA 46866
Standard Packaging Quantity	5 pc
UPC	78285630651

ANSI is a registered trademark of American National Standards Institute. ASTM is a registered trademark of American Society for Testing and Materials. CSA, CSA-US and C-CSA-US are registered trademarks of Canadian Standards Association. NEMA is a registered service mark of National Electrical Manufacturers Association.

#### WARNING

ERICO products shall be installed and used only as indicated in ERICO's product instruction sheets and training materials. Instruction sheets are available at [www.erico.com](http://www.erico.com) and from your ERICO customer service representative. Improper installation, misuse, misapplication or other failure to completely follow ERICO's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death.

Copyright © 2015 ERICO International Corporation. All rights reserved.

CADDY, CADWELD, CRITEC, ERICO, ERIFLEX, ERITECH, and LENTON are registered trademarks of ERICO International Corporation.



**ERICO**