

THERMOSTAT

LINE VOLTAGE - RJ32 SERIES

COLOURS

white or beige

DIMENSIONS

4 1/2 in. x 2 3/4 in. x 2 1/4 in. (114.3 mm x 69.9 mm x 57.2 mm)

VOLTAGE

22 A @ 120, 208 or 240 Vac / 19 A @ 277 Vac

CONTROL

- 2-wire connection (single pole model) or 4-wire connection (double pole model)
- temperature in degrees Celsius

TEMPERATURE RANGE

between 5 and 32 °C (41 and 90 °F)



PRODUCT	DESCRIPTION	COLOUR	PRICE
RJ32W1	SINGLE POLE THERMOSTAT	WHITE	12.75
RJ32B1	SINGLE POLE THERMOSTAT	BEIGE	12.75
RJ32W2	DOUBLE POLE THERMOSTAT	WHITE	20.00

