

335BK

## marrette®

The Marrette XTP is a high quality, twist-on wire connector with a unique spring and cap grip design that sets it apart from the competition.



### General

Type:	XTP
T&B UPC:	06739600797
T&B Status:	M
Electrical Rating:	Models nos. 329 and 330 are approved for circuits up to 300 V only. Models nos. 331, 333, 335 and 822 are approved for circuits up to 600 V, and lighting fixtures and signs up to 1000 V.
Inner Material:	Live action variable volume spring
External Cap Features:	Posi-Grip surface combines a matte finish with closely-spaced, deep grooves for superior twisting power, even when hands are greasy or damp.
Inner Spring Features:	Exclusive Live Action variable volume spring expands to accommodate more wires with less twisting effort, compared to other connectors with a "fixed spring" design.
Conductor:	Copper only
Temperature Rating:	105°C
Colour:	Red
Material:	Tough durable polypropylene

### Packaging Information

Packaging Format:	Flip-Pak
Quantity per Package:	7000
Std. Pkg. (Min/Mult):	7000 Units

### Dimension Information

Wire Size:	22 - 10 AWG
------------	-------------