

CI4004-FP5

IBERVILLE®

Nonmetallic connector 1/2 in.



General

Type:	Nonmetallic Sheathed Cable
Application:	For 14/2-10/2; 14/3-10/3 2 cables: 14/2-12/2
T&B UPC:	62253807872
T&B Status:	M
Material:	Plastic

Dimension Information

Clamping Range max.:	0.42 in.
Clamping Range min.:	0.21 in.
Trade Size:	1/2 in.