

35D



## marrette®

The Marrette Black High Temperature rating makes it the best solution for high wattage lighting fixtures and signs.

### General

|                        |   |
|------------------------|---|
| Type:                  | Black High Temperature  |
| T&B UPC:               | 06739601499   |
| T&B Status:            | M   |
| Electrical Rating:     | For circuits up to 600 V, and lighting fixtures and signs up to 1000 V.   |
| Inner Material:        | Copper-coated spring  |
| External Cap Features: | Large, finely ribbed, "barrel-shaped" - Deep wide throat - Threaded entry |
| Inner Spring Features: | Conical design  |
| Conductor:             | Copper only   |
| Temperature Rating:    | 150°C   |
| Colour:                | Black   |
| Material:              | Rugged thermoplastic polymer  |

### Packaging Information

|                       |           |
|-----------------------|-----------|
| Packaging Format:     | Flip-Pak  |
| Quantity per Package: | 500       |
| Std. Pkg. (Min/Mult): | 500 Units |

### Dimension Information

|            |            |
|------------|------------|
| Wire Size: | 18 - 8 AWG |
|------------|------------|