

BE6-V



Multiple position-Horizontal 100 A per position. 4 jaw left-hand entry.



General

Type:	BE2, BEC Series
Meter Position:	6 Position
Notes for picture:	Picture represents the BE2 Series. Please refer to the specifications.
Application:	All Provinces
T&B UPC:	62487100202
T&B Status:	M
Voltage Rating:	600 V
Amperage Rating:	200 A

Dimension Information

Conductor Range:	Line: 6 AWG -250 kcmil / Load : 6-1/0 AWG
Height:	14-5/8 in.
Width:	43-3/4 in.