



Ocal®

T&B Catalog Number:

UPC Number:

Description:

ELL3/4-G

70450837040

3/4" x 90° Dark Gray 40 mil PVC Coated Hot-Dip Galvanized Rigid Steel Elbow.

Status:

Active

WEB_USE

-T&B Product Line 087

Features

- A minimum .040" (40 mil) PVC coating on the exterior.
- A nominal .002" (2 mil) blue urethane on the interior.
- Ocal-Blue standard radius elbows are factory bent to reduce the ti
- Special radiuses and degrees are available upon request.
- Color coded thread protectors on each end.
- Standard radiuses in 30°, 45°, 60° and 90°

General

-Custom_Finish sre_3490
 -Material Steel
 -Finish Hot Dip Galvanized
 -Color Dark Gray
 -Thread Protector Color Red

Dimension Information

-Pipe Size (inches) 3/4
 -Pipe Size (Metric Size Designator*) 21
 -Degree of Bend 90
 -Radius-R (inches) 4.50
 -Radius-R (mm) 114.3
 -Offset-C (inches) 7.25
 -Offset-C (mm) 184.15
 -Straight End-D (inches) 2.75
 -Straight End-D (mm) 69.85
 -Unbent Length (inches) 12.50
 -Unbent Length (mm) 317.5
 -Weight per Each (lbs) 1.07
 -Weight per Each (kil) 0.485

Technical Information

-Chemical Resistance Chart Available on Website

Specifications

-Ocal Specification Guide-1995 Master Form Available on Website
 -Ocal Specification Guide-1995 Master Form Available on Website
 -Ocal Specification Guide-2004 Master Form Available on Website
 -Ocal Specification Guide-2004 Master Form Available on Website

Packaging

-T&B Inner Pack 1
 -Package in Units 20
 -T&B Sold in UOM Each
 -T&B Weight Per UOM 1.24 lbs. Each

Application Support

-T&B Sales Drawings wsd-000551

-Recommended Installation Procedures	Available on Website
-NEMA Standards-RN 1	Available on Website
-NEC 310-16 - Conductors for General Wiring	Available on Website
-NEC Table 8	Available on Website

Notes

-*Note	Metric size designator (ANSI C80. 1-1994)
-**Note	Dimensional values are of un-coated elbows.
-***Note	Standard color is dark gray. Also available in white and light blue.

Certifications

-RoHS Compliance	No
------------------	----

Certifications



File Nbr:

E 46453

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com