

N6NY-004C-0-M



## Catamount™

Black Plain edge cable clamp. Width 0.500 in. / 12.7 mm. Fully radiused inside edges with size markings in inches and millimeters for easy identification.

### General

Type:	Cable Clamps and Clips
Application:	For use in temperatures ranging from -40 degree C to 85 degree C
T&B UPC:	72849407402
T&B Status:	M
Colour:	Black
Material:	Nylon 6/6

### Dimension Information

Thickness:	0.06 in. / 1.52 mm
Temperature Range:	-40°F to 185°F (-40°C to 85°C)
Mounting Hole Size:	#10
Closed Diameter:	0.25 in. / 6.35 mm
Width:	0.5 in. / 12.7 mm