



Fork Terminal T&B Catalog Number:

TV14-10F-XV

UPC Number:

72849414419

Status:

Active

Description:

Insulated Vinyl Fork Terminal for Wire Range 16-14 Stud Size #10, Blue, Canister

Features

Molded Funnel Entry Insulator. Brazed Seam. Internal Barrel Serrations.

General

Insulation Type	Insulated Vinyl
Material	Copper
Finish	Electro -Tin Plated
Color	Blue
Wire Range	16-14
Stud Size	#10

Dimension Information

d1 (inches)	.091
D (inches)	.177
E (inches)	.433
F (inches)	.256
L (inches)	.866
T (inches)	.031
W (inches)	.311

Specifications

Temperature Rating	75°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0

Tooling


Application Tools	WT112M, CM2000A
-------------------	-----------------

Packaging

T&B Order Multiple	75
T&B Inner Pack	75
Package in Units	900
Package Type	Canister
T&B Sold in UOM	Each
T&B Weight Per UOM	5 lbs. per 1000
Alternate Package Qty	TV1410FL

Certifications

RoHS Compliance	Yes
-----------------	-----



For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com