



H-Tap Connectors T&B Catalog Number:

UPC Number:
Status:
Description:

WR815
78378610022
Active

Aluminum Wide Range H-Type Compression Connector Main: 477 18/1-4/0 ACSR, 556-250 Str., Tap: 2/0-6 ACSR, 2/0-6 Str., 3/0-6 Sol., Die: N

Features

- Made of 1350 Aluminum alloy to provide high strength and conductivity. Prefilled with oxide inhibitor held captive in the rib/connection area.
- Enables excellent connector contact without distorting the conductor's shape.
- Fold-in tabs provide positive tab interlock as tool closes.
- RUS accepted and complies with ANSI C119.4

General

Style	Type WR - Wide Range N Die Tap Connectors
Material	Aluminum
Standard Conductor Main - ACSR	477 18/1, 397, 336, 266, 4/0
Standard Conductor Main - Stranded	556, 500, 400, 397, 350, 336, 300, 266, 250
Standard Conductor Tap - ACSR	2/0, 1/0, 1, 2, 3, 4, 6
Standard Conductor Tap - Stranded	2/0, 1/0, 1, 2, 3, 4, 6
Standard Conductor Tap - Solid	3/0, 2/0, 1/0, 1, 2, 3, 4, 6
Compact Conductor Main - ACSR	556, 477, 397, 336, 266
Compact Conductor Main - Stranded	556, 477, 397, 336, 266, 250
Compact Conductor Tap - ACSR	2/0, 1/0, 1, 2, 3, 4, 6
Compact Conductor Tap - Stranded	3/0, 2/0, 1/0, 1, 2, 3, 4, 6

Dimension Information

Length (inches)	2"
Conductor Diameter Main Max.	0.858
Conductor Diameter Main Min.	0.520
Conductor Diameter Tap Max.	0.447
Conductor Diameter Tap Min.	0.162

Tooling

Application Tools	JB12B, TBM14M, 12A, Y-35
No. Indents Hydraulic Tool	2

Packaging


T&B Inner Pack	10
Package in Units	80
T&B Sold in UOM	Each
T&B Weight Per UOM	32.85 lbs. per 100

Notes

- Will accept standard conductors of the same size with a 3 percent reduction of compressed diameter.
- All die connectors are for use with hydraulic tools, 12-ton and greater.
- Fig. 1

Certifications

RoHS Compliance	Yes
-----------------	-----



For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com