

Distribution Compression Splice

T&B Catalog Number:

RC20

UPC Number:

78378605121

Status:

Active

Description:

Aluminum 16 inch Full-Tension Distribution Compression Splice for Wire Range: 2/0 ACSR(6/1), 2/0 AAAC(7), 2/0 5005(7), 2/0 AAC(7), Mechanical Dies: 781, Hydraulic Dies: B74AH, 659, 3/4



Features

- Center stop ensures proper conductor positioning.
- External end taper provides conductor stress relief, ease of stringing and corona protection.
- Internal end chamfer enables easy conductor insertion and prevents sharp edge contact with conductor.
- Standards compliant. Meets ANSI C119.4 requirements - withstands 95 percent of conductor rated breaking strength.

General

Style	Full-Tension
Material	Aluminum
Wire Size	2/0 ACSR(6/1), 2/0 AAAC(7), 2/0 5005(7), 2/0 AAC(7)

Dimension Information

Length (inches)	16
-----------------	----

Tooling

Mechanical Tool OD58 Dies	781
Mechanical Tool OD58 Crimps Per End	32
Mechanical Tool O-52 Dies	781
Mechanical Tool O-52 Crimps Per End	32
Hydraulic Tool JB12B Dies	B74AH
Hydraulic Tool JB12B Crimps Per End	Overlap
Hydraulic Tool Y Series Dies	659
Hydraulic Tool Y Series Crimps Per End	Overlap
Hydraulic Tool WH Series Dies	3/4
Hydraulic Tool WH Series Crimps Per End	Overlap

Packaging

Package in Units	25
T&B Sold in UOM	Each
T&B Weight Per UOM	62.6 lbs. per 100

Notes

OD58 Dies are interchangeable with those listed for O-52.

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com