



Dual-Rated T&B Catalog Number:

UPC Number:
Status:
Description:

ADR11-21
78378661005
Active

Type ADR-ALCUL Two-Conductor, One-Hole Mount for Conductor Range
Max 1/0 Str., Min 14 AWG

Features

Easy Installation - no special tools required.

General

Style	ALCUL Two-Conductor, One-Hole Mount
Material	Aluminum
Plating	Tin-Plated
Conductor Range (AL or CU) Maximum	1/0 Str.
Conductor Range (AL or CU) Minimum	14 AWG

Dimension Information

Length (inches)	1 15/32
Width (inches)	1 7/32
Height (inches)	25/32
D (inches)	7/16
E (inches)	1/4
F (inches)	3/16
G (inches)	27/32
I (inches)	35/64

Packaging

T&B Inner Pack	12
Package in Units	120
T&B Sold in UOM	Each
T&B Weight Per UOM	6.5 lbs. per 100

Notes

UL 486B tested, AL9CU rated

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:

E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com