



Aluminum Splice

T&B Catalog Number:

ASP2
78378661061
Active

UPC Number:
Status:
Description:

Aluminum Splice - max 35KV, 2 Str. Wire, Length 1 7/8 in., Tin Plated, Pink

Features

- Made of high-conductivity seamless aluminum tubing. Tin plated for corrosion resistance.
- Specifically chamfered barrel for ease of installation.
- Color-coded for matching die identification. Prefilled with oxide inhibiting compound.
- UL Listed when installed with Blackburn, Burndy, T&B or Andersons Tools.

General

Material	Aluminum
Finish	Tin Plated
Wire Size	2 Str.
Barrel Length	Standard
Die Color	Pink

Dimension Information

Length (inches)	1 7/8
-----------------	-------

Specifications

Voltage Rating	35KV
----------------	------

Tooling

Connector & Tooling Chart	Available on Website
---------------------------	----------------------

Packaging

T&B Inner Pack	10
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	3.4 lbs. per 100

Application Support

T&B Instruction Sheets	ta01325-tb2
------------------------	-------------

Notes

For use with aluminum conductor (concentric, compressed or compact). Also listed for use with copper conductor.

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
Y

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com