



## H-Tap Connectors T&B Catalog Number:

WR139  
78378610036  
Active

## UPC Number: Status: Description:

Aluminum Wide Range H-Type Compression ConnectorS Main: 1/0 - 4 ACSR, 2/0 - 3 Str., 2/0 - 2 Sol. Tap: 8 -10 Str., 6 - 10 Sol., Groove C: 12 - 14 Str., 12 -14 Sol. Die: O

### Features

- Made of 1350 Aluminum alloy to provide high strength and conductivity. Prefilled with oxide inhibitor held captive in the rib/connection area.
- Enables excellent connector contact without distorting the conductor's shape.
- Fold-in tabs provide positive tab interlock as tool closes.
- RUS accepted and complies with ANSI C119.4

### General

Style	Type WR - Wide Range Street Lighting Tap Connectors
Material	Aluminum
Standard Conductor Main - ACSR	1/0, 1, 2, 3, 4
Standard Conductor Main - Stranded	2/0, 1/0, 1, 2, 3
Standard Conductor Main - Solid	1, 2

### Dimension Information

Length (inches)	1 1/2"
Conductor Diameter Main Max.	0.419
Conductor Diameter Main Min.	0.250

### Tooling

Connector Die	O
No. Indents Mechanical Tool	4
No. Indents Hydraulic Tool	2

### Packaging

T&B Inner Pack	25
Package in Units	250
T&B Sold in UOM	Each
T&B Weight Per UOM	8.8 lbs. per 100

### Notes

- Will accept standard conductors of the same size with a 3 percent reduction of compressed diameter.
- Fig. 1

### Certifications

RoHS Compliance	Yes
-----------------	-----



For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com