



**Dual-Rated  
T&B Catalog Number:**

ADR50-32  
78378661029

**UPC Number:**

**Status:**

Active

**Description:**

Type ADR-ALCUL Three-Conductor, Two-Hole Mount for Conductor Range Max 500 kcmil, Min 4 Str.

**Features**

Easy Installation - no special tools required.

**General**

Style	ALCUL Three-Conductor, Two-Hole Mount
Material	Aluminum
Plating	Tin-Plated
Conductor Range (AL or CU) Maximum	500 kcmil
Conductor Range (AL or CU) Minimum	4 Str.

**Dimension Information**

Length (inches)	4 11/16
Width (inches)	3 3/4
Height (inches)	1 9/16
D (inches)	5/8
E (inches)	1/2
F (inches)	7/16
G (inches)	3 5/16
I (inches)	1 1/4

**Packaging**

T&B Inner Pack	3
Package in Units	30
T&B Sold in UOM	Each
T&B Weight Per UOM	1.21 lbs. Each

**Notes**

NEMA spacing 1 3/4 inch centers.

Connectors accomodating conductors 600 kcmil and larger have double rows of set screws (D suffix).

UL 486B tested, AL9CU rated

**Certifications**

RoHS Compliance	Yes
-----------------	-----

**Certifications**



File Nbr:  
E9809

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com