



**Dual-Rated  
T&B Catalog Number:**

ADR60-22D

**UPC Number:**

78378661034

**Status:**

Active

**Description:**

Type ADR-ALCUL Two-Conductor, Two-Hole Mount for Conductor Range Max 600 kcmil, Min 2 Str.

**Features**

Easy Installation - no special tools required.

**General**

Style	ALCUL Two-Conductor, Two-Hole Mount
Material	Aluminum
Plating	Tin-Plated
Conductor Range (AL or CU) Maximum	600 kcmil
Conductor Range (AL or CU) Minimum	2 Str.

**Dimension Information**

Length (inches)	5 5/16
Width (inches)	2 3/4
Height (inches)	1 1/2
D (inches)	5/8
E (inches)	1/2
F (inches)	3/8
G (inches)	3 1/16
I (inches)	1 7/16

**Packaging**

T&B Inner Pack	3
Package in Units	30
T&B Sold in UOM	Each
T&B Weight Per UOM	90.69 lbs. per 100

**Application Support**

T&B Sales Drawings	wsd-000390
--------------------	------------

**Notes**

- NEMA spacing 1 3/4 inch centers.
- Connectors accomodating conductors 600 kcmil and larger have double rows of set screws (D suffix).
- UL 486B tested, AL9CU rated

**Certifications**

RoHS Compliance	Yes
-----------------	-----

**Certifications**



File Nbr:  
E9809

**For further technical assistance, please contact us...**

Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

8155 T&B Blvd.  
Memphis, TN 38125

Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)