



Split-Bolt
T&B Catalog Number:

8H
 78378620002
 Active

UPC Number:
Status:
Description:

Type H High Strength Split-Bolt Connector made of Bronze Alloy for Use on Copper Conductors. Conductor Range for Equal Main and Tap 8 Str.-10 Sol.

Features

Bolt and nut of high-strength corrosion-resistant bronze alloy. Copper pressure bar. Bolt and nut of hex design.

Standards

UL, CSA

Application

Splicing, tapping or terminating conductors in power and grounding electrical connection.

General

| | |
|-------------------------------------------------------|--------------|
| Style | Type H |
| Wire Type | Copper |
| Material | Bronze Alloy |
| Color | Metallic |
| Conductor Range for Equal Main and Tap 8 Str.-10 Sol. | |
| Conductor Range Min. Tap with one Max. 14 Sol. | |
| Main | |

Dimension Information

| | |
|------------|-------|
| A (inches) | 3/8 |
| B (inches) | 0.146 |
| C (inches) | 1/2 |
| D (inches) | 25/32 |

Packaging

| | |
|--------------------|-------------------|
| T&B Inner Pack | 100 |
| Package in Units | 1000 |
| T&B Sold in UOM | Each |
| T&B Weight Per UOM | 2.56 lbs. per 100 |

Notes

UL recognizes solid and stranded conductor configurations for sizes #8 and smaller and stranded configurations only for sizes #6 and larger.

Certifications

RoHS Compliance Yes

Certifications



File Nbr:
 E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com