



Disconnects T&B Catalog Number:

UPC Number:
Status:
Description:

TV14-250FD-XV
72849414427
Active

Insulated Vinyl Female - 250 Series Disconnects for Wire Range 16-14, Blue, Canister

Features

Easy entry copper insulation sleeve.

General

Disconnect Type	Female - 250 Series
Insulation Type	Insulated Vinyl
Material	Brass with Copper Sleeve
Color	Blue
Wire Range	16-14
Tab Size	.250 x .032

Dimension Information

B (inches)	.413
D (inches)	.187
F (inches)	.287
L (inches)	.819
T (inches)	.016
W (inches)	.260

Specifications

Temperature Rating	105°C
Voltage Rating	300V
Flammability Rating	UL 94 V-0

Tooling

Application Tools	WT112M
-------------------	--------

Packaging

T&B Order Multiple	75
T&B Inner Pack	75
Package in Units	900
Package Type	Canister
T&B Sold in UOM	Each
T&B Weight Per UOM	0.63 lbs. per 1000
Alternate Package Qty	TV14250FDL

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com