



H-Tap Connectors T&B Catalog Number:

UPC Number:
Status:
Description:

WR159
78378610001
Active

Aluminum Wide Range H-Type Compression Connector Main: 2-6 ACSR, 1-6 Str., 2-6 Sol. Tap: 2-6 ACSR, 1-6 Str., 2-6 Sol. Die: O

Features

Made of 1350 Aluminum alloy to provide high strength and conductivity. Prefilled with oxide inhibitor held captive in the rib/connection area.

Enables excellent connector contact without distorting the conductor's shape.

Fold-in tabs provide positive tab interlock as tool closes.

RUS accepted and complies with ANSI C119.4

General

Style	Type WR - Supplemental O and D Die Connectors
Material	Aluminum
Standard Conductor Main - ACSR	2, 4, 6
Standard Conductor Main - Stranded	1, 2, 3, 4, 6
Standard Conductor Main - Solid	2, 4, 6
Standard Conductor Tap - ACSR	2, 4, 6
Standard Conductor Tap - Stranded	1, 2, 3, 4, 6
Standard Conductor Tap - Solid	2, 4, 6
Compact Conductor Main - ACSR	1, 2, 4, 6
Compact Conductor Main - Stranded	1, 2, 3, 4, 6
Compact Conductor Tap - ACSR	1, 2, 4, 6
Compact Conductor Tap - Stranded	1, 2, 3, 4, 6

Dimension Information

Length (inches)	1 7/16"
Conductor Diameter Main Max.	0.332
Conductor Diameter Main Min.	0.162
Conductor Diameter Tap Max.	0.332
Conductor Diameter Tap Min.	0.162

Tooling

Application Tools	JB12A, JB12B, 12A, Y-35
Connector Die	O
No. Indents Mechanical Tool	4
No. Indents Hydraulic Tool	2

Packaging

T&B Inner Pack	25
Package in Units	250
T&B Sold in UOM	Each
T&B Weight Per UOM	8.56 lbs. per 100

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com