



Automatic Splices T&B Catalog Number:

ATS397477

UPC Number:

78378610384

Status:

Active

Description:

Autoset Automatic Tension Splice for Wire Range: 336 26/7, 397 18/1, 397 26/7, 477 18/1 ASCR, 394.5 AAAC, 397-477 AAC, Aluminum, Color Code Blue

Features

Color-coded end pieces provide for visual identification of maximum conductor size. Color-coded tape further eliminates errors and speeds up installations. Funnel shape swiftly guides conductor into position for insertion.

Pilot cap envelops strands and guides conductor past serrated jaws and into the center of the splice.

Die-cast, precision-made jaws provides optimum contact area for a greater range of conductor sizes. Compression spring positions the jaw for positive conductor acceptance.

High-Strength aluminum alloy tubing covers the connection for superior corrosion protection and long-lasting durability. Tubular center stop automatically determines proper insertion length of both conductors.

General

Style	ATS Autoset
Material	Aluminum
Conductor Range - ASCR	336 26/7, 397 18/1, 397 26/7, 477 18/1
Conductor Range AAAC	394.5
Conductor Range AAC	397-477
Color Code	Blue

Dimension Information

Length (inches)	23 1/2
-----------------	--------

Packaging

T&B Inner Pack	1
Package in Units	10
T&B Sold in UOM	Each
T&B Weight Per UOM	170.5 lbs. per 100

Application Support

T&B Instruction Sheets	027-365-02-tb2
------------------------	----------------

Notes

Application limited to a maximum 10,000 lb. tensile.

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125

T&B Technical Support
MS 3B-50
8155 T&B Blvd.

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289

