



## Dual-Rated T&B Catalog Number:

ADR25  
78378661010  
Active

## UPC Number: Status: Description:

Type ADR-ALCUL Single-Conductor, One-Hole Mount for Conductor Range Max 250 kcmil, Min 6 Str.

### Features

Easy Installation - no special tools required.

### General

Style	ALCUL Single-Conductor, One-Hole Mount
Material	Aluminum
Plating	Tin-Plated
Conductor Range (AL or CU) Maximum	250 kcmil
Conductor Range (AL or CU) Minimum	6 Str.

### Dimension Information

Length (inches)	2
Width (inches)	1
Height (inches)	1 1/8
D (inches)	15/32
E (inches)	5/16
F (inches)	1/4
G (inches)	1

### Packaging

T&B Inner Pack	25
Package in Units	250
T&B Sold in UOM	Each
T&B Weight Per UOM	11.75 lbs. per 100

### Application Support

T&B Sales Drawings	wsd-000391
--------------------	------------

### Notes

5/16 Socket screw on sizes 250 through 350 kcmil.  
UL 486B tested, AL9CU rated

### Certifications

RoHS Compliance	Yes
-----------------	-----

### Certifications



File Nbr:  
E9809

For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com