



Short Barrel Copper Lug T&B Catalog Number:

UPC Number:
Status:
Description:

CTL250-12
78378613190
Active

Copper One-Hole Lug - Straight Short Barrel - max 35KV, 250 kcmil Wire, 1/2 Bolt Size, Tin Plated, Yellow

Features

Made of high-conductivity seamless copper tubing. Tin plated for corrosion resistance.

Specifically chamfered barrel for ease of installation.

Color-coded for matching die identification.

UL Listed for AWG conductor when installed with Blackburn, Burndy, T&B or Andersons Tools.

Complies with Subpart 111.60-17 of Federal Register's Coast Guard Electrical Engineering Rules and Regulations.

General

| | |
|-----------------|------------|
| Material | Copper |
| Finish | Tin Plated |
| Wire Size | 250 kcmil |
| Number of Studs | 1 |
| Stud Size | 1/2 |
| Tongue Angle | Straight |
| Barrel Length | Short |
| Barrel Shape | Standard |
| Die Color | Yellow |

Dimension Information

| | |
|------------|---------|
| A (inches) | 1 1/32 |
| B (inches) | 1 1/4 |
| C (inches) | 1/2 |
| L (inches) | 2 19/32 |
| T (inches) | 1/8 |
| W (inches) | 1 1/8 |

Specifications

| | |
|----------------|------|
| Voltage Rating | 35KV |
|----------------|------|

Tooling

| | |
|---------------------------|----------------------|
| Connector & Tooling Chart | Available on Website |
|---------------------------|----------------------|

Packaging

| | |
|--------------------|-----------------|
| T&B Inner Pack | 10 |
| Package in Units | 100 |
| T&B Sold in UOM | Each |
| T&B Weight Per UOM | 13 lbs. per 100 |

Notes

For use with copper conductor: AWG, stranded, flexible cable, welding cable and portable cord. Specially designed for industrial and building applications.

Certifications

RoHS Compliance Yes

Certifications



File Nbr:

Y

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com