



**Aluminum Splice**  
**T&B Catalog Number:**

ASP4  
 78378661062  
 Active

**UPC Number:**  
**Status:**  
**Description:**

Aluminum Splice - max 35KV, 4 Str. Wire, Length 1 7/8 in., Tin Plated, Green

**Features**

- Made of high-conductivity seamless aluminum tubing. Tin plated for corrosion resistance.
- Specifically chamfered barrel for ease of installation.
- Color-coded for matching die identification. Prefilled with oxide inhibiting compound.
- UL Listed when installed with Blackburn, Burndy, T&B or Andersons Tools.

**General**

Material	Aluminum
Finish	Tin Plated
Wire Size	4 Str.
Barrel Length	Standard
Die Color	Green

**Dimension Information**

Length (inches)	1 7/8
-----------------	-------

**Specifications**

Voltage Rating	35KV
----------------	------

**Tooling**

Connector & Tooling Chart	Available on Website
---------------------------	----------------------

**Packaging**

T&B Inner Pack	10
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	3 lbs. per 100

**Application Support**

T&B Instruction Sheets	ta01325-tb2
------------------------	-------------

**Notes**

For use with aluminum conductor (concentric, compressed or compact). Also listed for use with copper conductor.

**Certifications**

RoHS Compliance	Yes
-----------------	-----

**Certifications**



File Nbr:  
 Y

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)