



## Service Entrance Splices

**T&B Catalog Number:**

KL36-1

**UPC Number:**

78378605001

**Status:**

Active

**Description:**

Aluminum 3 1/2" Service Entrance Compression Splice for Wire Range - End A: 1/0 ASCR, 1/0 Str., 2/0 Str. Compact, Yellow, End B: 1/0 ASCR, 1/0 Str., 2/0 Str. Compact, Yellow, Die: 840

### Features

Use for combinations of aluminum-to-aluminum and aluminum-to-copper conductors. Can be used as a low-cost reducing sleeve.

Center stop to ensure proper conductor positioning. Color-coded and marked for easy identification.

Standards compliant. Meets ANSI C119.4 requirements.

### General

Insulation Type	Non-Insulated
Material	Aluminum
Barrel Length	Longer Length
Conductor Range A ASCR	1/0
Conductor Range A Str./Sol.	1/0 Str., 2/0 Str. Compact
Conductor Range B ASCR	1/0
Conductor Range B Str./Sol.	1/0 Str., 2/0 Str. Compact
Conductor A Color	Yellow
Conductor B Color	Yellow

### Dimension Information

Length (inches)	3.5
Conductor A Diameter Max.	0.398
Conductor A Diameter Min.	0.368
Conductor B Diameter Max.	0.398
Conductor B Diameter Min.	0.368

### Tooling

Die Series	840 Die Series
Hydraulic Dies	840, U-K840 U-249, B49EA
Mechanical Dies	840, W-K840 EEI-11A, TX

### Packaging

T&B Inner Pack	25
Package in Units	250
T&B Sold in UOM	Each
T&B Weight Per UOM	19.28 lbs. per 100

### Certifications

RoHS Compliance	Yes
-----------------	-----

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: techsupport@tnb.com