

ETH-SP-EG



Universal splice. Electro-galvanized steel



General

| | |
|-------------------|---|
| Type: | Splices |
| Application: | The most widely used connection method for non-radiused bends or joints |
| T&B UPC: | 62649099513 |
| T&B Status: | M |
| Special Features: | Tool required: 10 mm nut driver |
| Material: | Electro-galvanized steel |

Packaging Information

| | |
|-----------|----|
| Std pack: | 25 |
|-----------|----|

Dimension Information

| | |
|---------------|------|
| Weight kg/ea: | 0.06 |
| Weight/Ea.: | 0.13 |