



Ground Rod Clamps T&B Catalog Number:

UPC Number:
Status:
Description:

JAB1H
78378680288
Active

Ground Rod Clamps Type JAB , Rod Size 1, Wire Range 8 Sol. - 4/0 Str.
Features

Cast of high-strength corrosion-resistant copper alloy. UL listed for direct burial.

Both hex head bolts and socket set screws available.

General

Style	Type JAB
Material	Copper
Wire Range	8 Sol. - 4/0 Str.
Thread Size	7/16 - 14 UNC-2A
Ground Rod	1

Dimension Information

Bolt Size (inches)	3
B (inches)	1 11/32
C (inches)	1 1/16
D (inches)	1

Packaging

T&B Inner Pack	1
Package in Units	50
T&B Sold in UOM	Each
T&B Weight Per UOM	23.38 lbs. per 100

Application Support

T&B Sales Drawings	wsd-000478
Overview	Available on Website

Notes

Add suffix P to Catalog number for tin-plated clamp.

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
Y

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com