



Split-Bolt T&B Catalog Number:

UPC Number:
Status:
Description:

APS41
78378620145
Active

Type APS Tin-Plated Aluminum Dual-Rated Split-Bolt Connector for Use on Copper, Aluminum Conductors. Conductor Range for Equal Main and Tap 4/0-2 Str.

Features

Installs with standard wrenches.

Application

Splicing, tapping or terminating conductors in power and grounding electrical connection.

General

Style	Type APS
Wire Type	Copper, Aluminum
Material	Aluminum
Plating	Electro Tin-Plated
Color	Metallic
Conductor Range for Equal Main and Tap 4/0-2 Str.	

Dimension Information

A (inches)	1
B (inches)	0.57
C (inches)	1 1/4
D (inches)	2.47
E (inches)	1 23/32

Packaging

T&B Inner Pack	25
Package in Units	150
T&B Sold in UOM	Each
T&B Weight Per UOM	25.14 lbs. per 100

Application Support

T&B Instruction Sheets	ta04215-tb2
------------------------	-------------

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com

