



## Two-Bolt Connector T&B Catalog Number:

2B500

**UPC Number:**

78378640005

**Status:**

Active

**Description:**

Copper Type 2B - Two-Bolt Connector without Spacer for Wire Range Main: 300 - 500 kcmil Tap: 4 Sol. - 500 kcmil , Bolt Size 3/4

### Features

Castings and bolts of high-strength copper alloy.  
Removable cap.

UL 486A listed for copper conductor only.

### General

Style	Type 2B - Two-Bolt Connector without Spacer
Material	Copper
Conductor Range AWG Main	300 - 500 kcmil
Conductor Range AWG Tap	4 Sol. - 500 kcmil

### Dimension Information

Bolt Size (inches)	3/4
D (inches)	1/2
H (inches)	2 1/2
L (inches)	2 1/4
Conductor Diameter B	.883 - 1.626

### Packaging

T&B Inner Pack	1
Package in Units	12
T&B Sold in UOM	Each
T&B Weight Per UOM	77.81 lbs. per 100

### Certifications

RoHS Compliance	Yes
-----------------	-----

### Certifications



File Nbr:

Y

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com