



Short Barrel Copper Lug
T&B Catalog Number:

CTL30-12
 78378613187
 Active

UPC Number:
Status:
Description:

Copper One-Hole Lug - Straight Short Barrel - max 35KV, 3/0 Str. Wire, 1/2 Bolt Size, Tin Plated, Orange

Features

- Made of high-conductivity seamless copper tubing. Tin plated for corrosion resistance.
- Specifically chamfered barrel for ease of installation.
- Color-coded for matching die identification.
- UL Listed for AWG conductor when installed with Blackburn, Burndy, T&B or Andersons Tools.
- Complies with Subpart 111.60-17 of Federal Register's Coast Guard Electrical Engineering Rules and Regulations.

General

Material	Copper
Finish	Tin Plated
Wire Size	3/0 Str.
Number of Studs	1
Stud Size	1/2
Tongue Angle	Straight
Barrel Length	Short
Barrel Shape	Standard
Die Color	Orange

Dimension Information

A (inches)	13/16
B (inches)	1 1/4
C (inches)	1/2
L (inches)	2 11/32
T (inches)	1/8
W (inches)	29/32

Specifications

Voltage Rating	35KV
----------------	------

Tooling

Connector & Tooling Chart	Available on Website
---------------------------	----------------------

Packaging

T&B Inner Pack	10
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	9.05 lbs. per 100

Notes

For use with copper conductor: AWG, stranded, flexible cable, welding cable and portable cord. Specially designed for industrial and building applications.

Certifications

RoHS Compliance Yes

Certifications



File Nbr:

Y

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com