



## Split-Bolt

**T&B Catalog Number:**

40H

**UPC Number:**

78378620017

**Status:**

Active

**Description:**

Type H High Strength Split-Bolt Connector made of Bronze Alloy for Use on Copper Conductors. Conductor Range for Equal Main and Tap 250 kcmil-1 Str.

### Features

Bolt and nut of high-strength corrosion-resistant bronze alloy. Copper pressure bar. Bolt and nut of hex design.

### Standards

UL, CSA

### Application

Splicing, tapping or terminating conductors in power and grounding electrical connection.

### General

Style Type H

Wire Type Copper

Material Bronze Alloy

Color Metallic

Conductor Range for Equal Main and Tap 250 kcmil-1 Str.

Conductor Range Min. Tap with one Max. 8 Sol.

Main

### Dimension Information

A (inches)	1
B (inches)	0.580
C (inches)	1 5/16
D (inches)	2 5/32

### Packaging

T&B Inner Pack	25
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	38 lbs. per 100

### Notes

UL recognizes solid and stranded conductor configurations for sizes #8 and smaller and stranded configurations only for sizes #6 and larger.

### Certifications

RoHS Compliance Yes

### Certifications



File Nbr:

E9809

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)