



Automatic Splices T&B Catalog Number:

ATS266336

UPC Number:

78378610383

Status:

Active

Description:

Autoset Automatic Tension Splice for Wire Range: 266 18/1, 266 26/7, 336 18/1 ASCR, 312.8 AAAC, 266-336 AAC, Aluminum, Color Code Green

Features

Color-coded end pieces provide for visual identification of maximum conductor size. Color-coded tape further eliminates errors and speeds up installations. Funnel shape swiftly guides conductor into position for insertion.

Pilot cap envelops strands and guides conductor past serrated jaws and into the center of the splice.

Die-cast, precision-made jaws provides optimum contact area for a greater range of conductor sizes. Compression spring positions the jaw for positive conductor acceptance.

High-Strength aluminum alloy tubing covers the connection for superior corrosion protection and long-lasting durability. Tubular center stop automatically determines proper insertion length of both conductors.

General

Style	ATS Autoset
Material	Aluminum
Conductor Range - ASCR	266 18/1, 266 26/7, 336 18/1
Conductor Range AAAC	312.8
Conductor Range AAC	266-336
Color Code	Green

Dimension Information

Length (inches)	23 1/2
-----------------	--------

Packaging

T&B Inner Pack	1
Package in Units	10
T&B Sold in UOM	Each
T&B Weight Per UOM	178 lbs. per 100

Application Support

T&B Instruction Sheets	027-365-02-tb2
------------------------	----------------

Notes

Application limited to a maximum 10,000 lb. tensile.

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125

T&B Technical Support
MS 3B-50
8155 T&B Blvd.

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289

