



**Split-Bolt**  
**T&B Catalog Number:**

350HPS  
78378685508  
Active

**UPC Number:**  
**Status:**  
**Description:**

Type HPS Plated Split-Bolt Connector with Spacer made of Copper Alloy for Use on Copper, Aluminum, ACSR Conductors. Conductor Range for Equal Main and Tap 350 kcmil-1/0 Str.

**Features**

Bolt and pressure bar of copper alloy, completely tin plated for corrosion resistance. Contoured spacer of bronze alloy copper.

**Application**

Splicing, tapping or terminating conductors in power and grounding electrical connection.

**General**

Style	Type HPS
Wire Type	Copper, Aluminum, ACSR
Material	Copper Alloy
Plating	Electro Tin-Plated
Color	Metallic
Conductor Range for Equal Main and Tap 350 kcmil-1/0 Str.	
Conductor Range Min. Tap with one Max. 2 Sol.	
Main	
Conductor Range For Equal Main and Tap ACSR	266.8-1/0

**Dimension Information**

A (inches)	1 5/16
B (inches)	0.717
C (inches)	1 21/32
D (inches)	2 11/16

**Packaging**

T&B Inner Pack	1
Package in Units	30
T&B Sold in UOM	Each
T&B Weight Per UOM	86.19 lbs. per 100

**Application Support**

T&B Sales Drawings	wsd-000072
--------------------	------------

**Notes**

Most connectors are UL and CSA Certified for copper conductor only.  
Blackburn Contax recommended when used on aluminum conductor.

**Certifications**

RoHS Compliance	Yes
-----------------	-----

## Certifications



File Nbr:  
E9809

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)