



Split-Bolt
T&B Catalog Number:

6H
 78378620004
 Active

UPC Number:
Status:
Description:

Type H High Strength Split-Bolt Connector made of Bronze Alloy for Use on Copper Conductors. Conductor Range for Equal Main and Tap 6 Sol.-8 Sol.

Features

Bolt and nut of high-strength corrosion-resistant bronze alloy. Copper pressure bar. Bolt and nut of hex design.

Standards

UL, CSA

Application

Splicing, tapping or terminating conductors in power and grounding electrical connection.

General

Style	Type H
Wire Type	Copper
Material	Bronze Alloy
Color	Metallic
Conductor Range for Equal Main and Tap 6 Sol.-8 Sol.	
Conductor Range Min. Tap with one Max. 14 Sol.	
Main	

Dimension Information

A (inches)	15/32
B (inches)	0.170
C (inches)	21/32
D (inches)	31/32

Packaging

T&B Inner Pack	100
Package in Units	600
T&B Sold in UOM	Each
T&B Weight Per UOM	5.06 lbs. per 100

Notes

UL recognizes solid and stranded conductor configurations for sizes #8 and smaller and stranded configurations only for sizes #6 and larger.

Certifications

RoHS Compliance Yes

Certifications



File Nbr:
 E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com